

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2001220110](#)  
**Status:** **Active**  
**Overview:** [Mega-Fit Power Connectors](#)  
**Description:** Mega-Fit Receptacle Backshell, Dual Row, Glow-Wire Capable, 10 Circuits

**Documents:**

[Drawing \(PDF\)](#) [Application Specification AS-76823-100-001 \(PDF\)](#)  
[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[3D Model \(PDF\)](#)

**General**

Product Family	Accessories
Series	<a href="#">200122</a>
Component Type	Backshell
Overview	<a href="#">Mega-Fit Power Connectors</a>
Product Name	Mega-Fit
UPC	889056291149

**Physical**

Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	4.150/g
Number of Rows	2
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

**Solder Process Data**


Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

Engineering Number	F4068.05-P28
--------------------	--------------

**Reference - Drawing Numbers**

Application Specification	AS-76823-100-001
Sales Drawing	2001220000-SD-000



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[200122](#) Series

**Use With**

Mega-Fit Receptacle Housing [170001](#)