

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0355642015](#)
Status: **Active**
Description: 1.02mm Tab Wire-to-Board Housing, Female, 20 Circuits

General

Product Family	Crimp Housings
Series	35564
Application	Signal, Wire-to-Board
Product Name	N/A
UPC	756054251157

Physical

Circuits (maximum)	20
Color - Resin	Gray, Natural
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Polyester
Net Weight	4.466/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Stackable	No
Temperature Range - Operating	-30° to +85°C

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-35564-001
Sales Drawing	SD-35564-001

EU ELV
Compliant

EU RoHS
Compliant

REACH SVHC
Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free
Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

China RoHS

Search Parts in this Series

[35564](#) Series

Mates With

[68151](#)

Use With

[50654](#) , [50655](#)