

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0834219051](#)  
**Status:** **Active**  
**Overview:** [Commercial Micro-D High-Density Connectors](#)  
**Description:** [Commercial Micro-D, CMD-to-CMD, 9 Circuits, Female - Female, 1.83m Length](#)

**Documents:**

[Drawing \(PDF\)](#) [Packaging Specification PK-83422-001 \(PDF\)](#)  
[Product Specification PS-83421-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">83421</a>
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Commercial Micro-D-to-Commerci
Overmolded	Yes
Overview	<a href="#">Commercial Micro-D High-Density Connectors</a>
Product Name	Commercial Micro-D
UPC	756054247167


**Physical**

Cable Length	1.83m
Circuits (Loaded)	9
Gender	Female-Female
Lock to Mating Part	None
Material - Plating Termination	Tin
Net Weight	1.102/g
Number of Rows	2
Packaging Type	Bag
Plating min - Mating	0.127µm
Plating min - Termination	1.270µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	.225mm (5.720") max.
Wire Size AWG	28
Wire/Cable Type	N/A

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-83422-001
Product Specification	PS-83421-001-001
Sales Drawing	SD-83421-004



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[83421](#) Series