

Product information

69 01 130

End Cutting Nipper

For mechanics

DIN ISO 5748

- With cutting edges for soft, hard and piano wire; also suitable for thin copper wires
- Lap joint
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



General

| | |
|-------------|--------------------|
| Article No. | 69 01 130 |
| EAN | 4003773017974 |
| Pliers | black atramentized |
| Head | polished |
| Handles | plastic coated |
| weight | 111 g |
| Dimensions | 130 x 50 x 48 mm |
| Standard | DIN ISO 5748 |

Classification

| | |
|----------------|------------|
| eCl@ss 5.1.4 | 21040302 |
| ETIM 5.0 | EC002222 |
| ETIM 6.0 | EC002222 |
| proficl@ss 6.0 | AAA947c004 |
| UNSPSC 13.1 | 27112117 |

technical change and errors excepted