3.81mm Pluggable Right Angle Header



RoHS

Compliant



Specifications


Current Rating


: 6 Amperes, 300V AC

Min. Insulation Withstand Voltage : 2,000V AC

Insulation Resistance : >2,000M Ω 500V DC Operating Temperature : -40°C to +105°C

Diagram





Dimensions: Millimetres (Inches)

Specification Table

No.	Material		Plating / Finish	Remark
1	Insulating Body	Polyamide 66	-	Green
2	Solder Pin	Brass	Tin Plated	

Dimensions Table

Pitch :	Pitch : 3.81mm (0.15inch)				
Poles	A (mm)	A (Inch)			
3	16.6	0.654			

Part Number Table

Description	Part Number	
Header 3.81mm Right Angle 6A 03 Way	ME030-50003	

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

