RJ45 Cat6 Faceplate Module pro-signal

RoHS **Compliant**

Features

Electrical

Voltage Rating : 125V AC RMS **Current Rating** : 1.5AMP Contact Resistance : 100MΩ max

Insulation Resistance : 1000 MΩ Min @500V DC : 750V AC RMS 60Hz, 1Min Dielectric Strength

Environmental

: -40°C to +85°C Storage Operation : 0°C to 70°C

Mechanical

Housing Material : ABS


PCB Material : FR-4 T=1.6mm **Contact Material** : Phosphor Bronze


Stamp Pin T=0.30mm


IDC Contact Material : Phosphore Bronze

T=0.50mm With Tin Plating

: 750 Ftimes Min RJ45 Jack; IFE IDC Life : 200 Ftimes Min Wire : AWG 22-26







Part Number Table

Description	Part Number
RJ45 Cat6 Faceplate Module	PSG3286

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence, pro-SIGNAL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

