

A9DC7616

residual current breaker with overcurrent protection (RCBO), Acti9 iCV40, 1P+N, 16 A, C Curve, 6000 A, 300 mA, A type



Main

Range	Acti9
Product name	Acti9 iCV40
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Device short name	ICV40N
Device application	Distribution
Poles description	1P + N
Number of protected poles	1
Neutral position	Left
[In] rated current	16 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type A
Breaking capacity	6000 A Icn at 230 V AC 50/60 Hz conforming to EN/IEC 61009-2-1
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Quality labels	KEMA-KEUR VDE EAC

Complementary

Device location in system	Outgoer
Network frequency	50/60 Hz
[Ue] rated operational voltage	230 V AC 50/60 Hz
Magnetic tripping limit	5...10 x In

Residual current tripping technology	Voltage independent
[Ics] rated service breaking capacity	6000 A 100 % x Icn at 230 V AC 50/60 Hz conforming to EN/IEC 61009-2-1
Rated breaking and making capacity	Idm 6000 A at 230 V AC 50/60 Hz conforming to EN 61009-2-1 Idm 500 A at 230 V AC 50/60 Hz conforming to IEC 61009-2-1
Limitation class	3 conforming to EN/IEC 61009-2-1
[Ui] rated insulation voltage	400 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	4 kV
Contact position indicator	Yes
Control type	Toggle
Local signalling	Fault indication ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top or bottom: tooth
9 mm pitches	4
Height	85 mm
Width	36 mm
Depth	73 mm
Net weight	210 g
Colour	White
Mechanical durability	20000 cycles
Electrical durability	20000 cycles
Locking options description	Padlocking device Sealable
Connections - terminals	Tunnel type terminals top or bottom 1...16 mm ² rigid Tunnel type terminals top or bottom 1...10 mm ² flexible
Wire stripping length	14 mm for top or bottom connection
Tightening torque	2 N.m top or bottom
Earth-leakage protection	Integrated

Environment

Standards	EN/IEC 61009-2-1
Product certifications	CE
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3
Overvoltage category	III conforming to IEC 60364
Electromagnetic compatibility	8/20 µs impulse withstand, 250 A conforming to EN/IEC 61009-2-1
Relative humidity	95 % at 55 °C
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	205 g
Package 1 Height	4 cm
Package 1 width	8.2 cm
Package 1 Length	10 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Weight	1.293 kg

Package 2 Height	11 cm
Package 2 width	9 cm
Package 2 Length	25 cm
Unit Type of Package 3	S03
Number of Units in Package 3	54
Package 3 Weight	12.103 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins