

## **WALL MOUNTED**

**ELECTROMAGNETIC FIRE DOOR HOLDERS** 

- INTEGRAL PART OF ANY FIRE ALARM SYSTEM
- 24VDC OR 230VAC SUPPLY VOLTAGE
- ZERO RESIDUAL FORCE
- 200N 500N HOLDING FORCE
- FIRE RESISTANT ABS CASING
- APPROVED TO EN1155 AND CE MARKED
- IP 51 PROTECTION
- HIGH QUALITY COST EFFECTIVE PACKAGE
- INCLUDES FITTING INSTRUCTIONS




Electromagnetic Fire Door Holders are designed to hold open Fire Doors in any areas where easy access is essential, and can be used in conjunction with any suitable fire alarm systems. When an alarm is triggered, power to the door holder is cut, allowing the fire door fitted with it's standard closing mechanism, to shut automatically. Type 87 door holders are fitted with an integral manual release button, allowing the door to be closed without operating the fire alarm.

The Type 87 door holder is surface mounted, and is housed in a white Fire resistant ABS casing. Type tested to meet EN1155, knockouts for surface or back cable entry, and a spring loaded pin to give zero residual holding force when de-energised.


The 230Vac unit includes a filter for EMC emissions and is CE marked. Internal diodes dissipate any "back EMF" on switch-off, reducing wear at the control unit.

The Type 87 is ideal for use in any public access areas including Hospitals, Offices, Hotels and Nursing Homes. Also available as shown below in a decorative finish.










TECHNICAL INFORMATION				
Voltage	24Vd.c. or 230a.c.			
Holding Force	200N or 500N			
Power Rating	1.15W			
Residual Holding force	Zero			
Ambient Temperature	0 - 40°C			
Protection	IP 51			
Fuse	20 mm / 500 mA			
Casing	White Fire-Res'nt ABS			
Weight	360g			

## **ORDER CODE:**

200N: 87-0351 (24 Vdc). 87-0352 (230 Vac)

500N: 87-0551 (24 Vdc)



TYPE 87 FLOOR MOUNTING BRACKET				
3 - Holes on Ø50.8 PCD  3 - Holes on Ø20  26.5				
CHAIN KEEPER				
3 - Holes ø 5.0 on 36.0 PCD	MOUNTING PLATE KEEPER PLATE			
Dia. 47.6	4.0 1m Chain Supplied 13.0			

Item Name	Order code	H1
Type 87 Stand	87-3020 87-3030 87-3050	200 300 500
Type 87 F.M. Bracket	34-035E	n/a
Chain Keeper	31-0308	n/a

Keeper Plates	Holding Force	Adjustment	Order Code
Low Profile	200N	15°	2-31-0306-Z231
Adjustable	200N	45°	2-31-0310-U003
Sprung	500N	15°	2-31-0507-Z003
Adjustable	500N	45°	2-31-0507-N001
Low Profile	500N	15°	2-31-0507-N002

## **ACCESSORIES**

Each type 87 is supplied with an adjustable keeper plate as standard. All other accessories should be sold seperately. Type 87 Chained Keeper Plates can be used where the standard keeper plate will not reach the door holder due to the door being positioned further towards the centre of the wall.