

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2153201062](#)
Status: **Active**
Overview: Mini-Fit Family Power Connectors
Description: Mini-Fit Jr. Female-to-Mini-Fit Jr. Female Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm Length, Tin (Sn) Plating, 6 Circuits, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family Cable Assemblies
Series [215320](#)
Application Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration Dual Ended Connectors
Connector to Connector Mini-Fit Jr. Both Ends
Overview [Mini-Fit Family Power Connectors](#)
Product Name Mini-Fit Jr.
Type Discrete Wire Assembly
UPC 193264596775

Physical

Cable Length 300.00mm
Circuits (Loaded) 6
Color - Resin Black
Gender Female-Female
Lock to Mating Part Yes
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 47.360/g
Number of Rows 1
Packaging Type Bag
Pitch - Mating Interface 4.20mm
Plating min - Mating 0.889µm
Plating min - Termination 0.889µm
Single Ended No
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 1.80-3.10mm
Wire Size AWG 16
Wire/Cable Type UL 1015

Electrical

Current - Maximum per Contact 9.0A
Voltage - Maximum 600V

Material Info

Reference - Drawing Numbers

Sales Drawing 2153201061-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[215320](#) Series

Mates With

Mini-Fit Jr. Headers [469990703](#) , [469990707](#)

Mini-Fit Jr. Plugs [469990657](#) ,
[469990658](#)