

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2138141102

Status:

Active

Overview:

Mega-Fit Power Connectors

Description:

Mega-Fit Plug Housing, Single Row, 2 Circuit, UL 94V-0, Glow-Wire Capable, Panel Mount

Documents:

Drawing (PDF)

Packaging Specification 2138140001-PK-000 (PDF)

Product Specification 1054171000-PS-000 (PDF)

Datasheet (PDF)

Application Specification 768232000-AS-000 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	213814
Application	Power, Wire-to-Wire
Overview	Mega-Fit Power Connectors
Product Name	Mega-Fit
UPC	193264466016
Physical	
Circuits (maximum)	2
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.990/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	5.70mm
Pitch - Termination Interface	5.70mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C, -40° to +120°C

Material Info

Reference - Drawing Numbers	
Application Specification	768232000-AS-000
Packaging Specification	2138140001-PK-000
Product Specification	1054171000-PS-000
Sales Drawing	2138140001-SD-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)4578-DC (25 June 2020)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

213814 Series

Mates With

Mega-Fit Receptacle Housing 200456

Use With

Mega-Fit TPA 105415
Mega-Fit Crimp Terminals 105417 , 105418

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION