Adapter BNC Jack - SMB Jack

multicomp PRO

RoHS

Compliant



Specifications:

Electrical: Frequency range Nominal impedance

: DC-4 GHz : 50Ω

Materials:

Bodies	: Brass per JIS-C3604		
Centre contact	: Brass per JIS-C3604		
Insulation	: PTFE per ASTM D1457 and ASTM D1710		


Mechanical:

Interface in accordance with : MIL-STD-348A.

Environmental:

Operating temperature range : -65°C to +165°C.

Diagram



Dimensions : Millimetres (Inches)

Part Number Table

Description	Part Type	Material	Finish	Part Number
Adapter, BNC Jack - SMB Jack	Body	Brass	Minimum Gold 3µ Inches	MP-R24-026-00-0032110MM
	Insulation	PTFE	None	
	Centre Contact	Brass	Minimum Gold 30µ Inches	
	Insulation	PTFE	None	
	Chassis	Brass	Minimum Gold 3µ Inches	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for white any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

