



From: Littelfuse Product Management

Subject: EOL notice

With regards to the above reference, due to concerns on assurance of supply, there would be an EOL of the below series of fuses now,

- 0402SFF series
- 0603SFF/0603SFS/0603SFV/0603SFP
- 1206SFF/1206SFS/1206SFH
- 2410SFV

Please see attached for the affected SAP part numbers.

We will also likely not be able to support existing orders.

Please let us know should you have further queries.

Best regards;  
Daniel Wang  
Director – Global Product Management - OverCurrent  
Electronics Business Unit  
Littelfuse Far East Pte Ltd  
(65) 6885 9199  
[Dwang@Littelfuse.com](mailto:Dwang@Littelfuse.com)

Parameter	1206SFP	483		
Electrical Overload Characteristic	100%: 4 hrs min.	100%: 4 hrs min.		
	200%: (1s - 60s)	250%: (5s Max)		
	1000%: (0.0002s - 0.02s)			
Voltage Rating	63Vdc (1A-2A)	75Vdc (0.375A-2A)		
	32Vdc (2.5A-5A)	65Vdc (3A-6.3A)		
	24Vdc (6A-8A)	32Vdc (7A-8A)		
Interrupting Rating @ rated voltage	50A (1A-5A)			
	80A (6A-8A)	50A (.375A-8A)		
I <sub>2t</sub>	375mA		0.027	
	500mA		0.065	
	750mA		0.150	
	1A	0.110		0.310
	1.25A			0.550
	1.5A	0.330		0.800
	2A	0.80		2.00
	2.5A	1.19		2.50
	3A	1.35		4.00
	3.15A			4.80
	3.5A	1.84		6.50
	4A	2.74		8.50
	4.5A	3.20		
	5A	5.50		13.00
	6A	12.50		
	6.3A			5.00
	7A	30.00		6.10
8A	60.00		11.00	

Parameter		1206SFF	437	466
Electrical Overload Characteristic		100%: 4 hrs min.	100%: 4 hrs min.	100%: 4 hrs min.
	250%: (5s Max)		250% (750mA-8A): (5s Max)	200%/ 5s max
	400%: (0.05s Max)		350% (250mA-500mA): (5s Max)	300%/ 0.2 s max
			350% (750mA-8A): (1s Max)	
Voltage Rating	63Vdc (0.5A-2A)		125Vdc (0.250A-.375A)	125Vdc (.125A-.375A)
	32Vdc (2.5A-5A)		63Vdc (.500mA - 2A)	63Vdc (.500mA - 2A)
	24 Vdc (6A-8A)		35 Vdc (2.5A-8A)	36 Vdc (2.5A-5A)
Interrupting Rating @ rated voltage	50A (0.5A-3A)		50A	50A
	45A (4A-8A)			
I <sub>2t</sub>	125mA			0.00064
	200mA			0.00055
	250mA		0.0030	0.0022
	375mA		0.0100	0.0045
	500mA	0.0021	0.0180	0.006
	750mA	0.0052	0.0640	0.0276
	1A	0.012	0.1000	0.0423
	1.25A		0.2560	0.064
	1.5A	0.025	0.3240	0.1103
	1.75A	0.045	0.0750	0.1835
	2A	0.070	0.2250	0.2326
	2.5A	0.140	0.4410	0.3516
	3A	0.220	0.5060	0.576
	3.5A		0.7770	
	4A	0.380	1.0240	1.764
	5A	0.600	2.3000	2.5
	6A	1.000		
7A	1.750	5.0200		
8A	2.500	7.2300		

Parameter		1206SFS	407
Electrical Overload Characteristic		100%: 4 hrs min.	100%: 4 hrs min.
		200%: (1s - 120s)	200%: (1s - 120s)
		300%: (0.1s - 3s)	300%: (0.1s - 3s)
		800%: (0.002s - 0.05s)	800%: (0.002s - 0.05s)
Voltage Rating		(1A-2A) - 63Vdc	(1A-2A) - 63Vdc
		(2.5A-5A) - 32Vdc	(2.5A-5A) - 32Vdc
		(5.5A-8A) - 24Vdc	(5.5A-8A) - 24Vdc
Interrupting Rating @ rated voltage		(1A-5.5A) - 50A	(1A-5.5A) - 50A
		(6A-8A) - 60A	(6A-8A) - 60A
I <sup>2</sup> t	1A	0.110	0.142
	1.25A	0.220	0.329
	1.5A	0.230	0.567
	2A	0.630	0.870
	2.5A	0.900	1.000
	3A	1.200	1.300
	3.5A	1.600	2.260
	4A	2.200	4.180
	4.5A	3.600	5.200
	5A	5.300	7.800
	5.5A	6.400	8.550
6A	8.500	15.560	
7A	10.000	16.230	
8A	16.900	24.120	

<b>Part Description</b>	<b>PN</b>
0402SFF100F/24-2	A57655-000
0402SFF150F/24-2	E46629-000
0402SFF200F/24-2	C93175-000
0402SFF300F/24-2	D22089-000
0402SFF400F/24-2	C99830-000
0603SFF050F/32-2	F49457-000
0603SFF050FM/32-2	F12705-000
0603SFF075F/32-2	C76908-000
0603SFF075FM/32-2	A97373-000
0603SFF100F/32-2	C65342-000
0603SFF100FM/32-2	A98660-000
0603SFF150F/32-2	C13581-000
PSR-28276	RF2841-000
0603SFF150FM/32-2	C41112-000
0603SFF200F/32-2	D95218-000
0603SFF200FM/32-2	E09311-000
0603SFF250F/32-2	C55743-000
0603SFF250FM/32-2	F48501-000
0603SFF300F/32-2	F71585-000
0603SFF300FM/32-2	D57360-000
0603SFF350F/32-2	C18343-000
0603SFF350FM/32-2	E09317-000
0603SFF400F/32-2	D36878-000
0603SFF400FM/32-2	E71947-000
0603SFF500F/32-2	F21397-000
0603SFF500FM/32-2	A73438-000
0603SFF600F/24-2	F97778-000
0603SFF600FM/24-2	E55805-000
1206SFF050F/63-2	D85866-000
1206SFF075F/63-2	D65792-000
1206SFF075FM/63-2	E97012-000
1206SFF100F/63-2	C01835-000
1206SFF100FM/63-2	D17193-000
1206SFF150F/63-2	A26865-000
1206SFF150FM/63-2	C88860-000
1206SFF175F/63-2	D10899-000
1206SFF175FM/63-2	A85118-000
1206SFF150F/63-2-A	RF2881-000
1206SFF200F/63-2	E63843-000
1206SFF200FM/63-2	A90427-000
1206SFF250F/32-2	E81894-000
1206SFF250FM/32-2	F51500-000
1206SFF300F/32-2	D20186-000
1206SFF300FM/32-2	E97044-000
1206SFF400F/32-2	C96949-000
1206SFF400FM/32-2	D56332-000
1206SFF500F/32-2	F10326-000

1206SFF500FM/32-2	C05228-000
1206SFF600F/24-2	C23196-000
1206SFF600FM/24-2	F22822-000
1206SFF700F/24-2	F32509-000
1206SFF700FM/24-2	E58515-000
1206SFF800F/24-2	F04779-000
1206SFF800FM/24-2	D90664-000
1206SFF600F/32-2	RF2327-000
1206SFF600FM/32-2	RF2328-000
1206SFF700F/32-2	RF2329-000
1206SFF700FM/32-2	RF2330-000
1206SFF800F/32-2	RF2331-000
1206SFF800FM/32-2	RF2332-000
0603SFS100F/32-2	RF0335-000
0603SFS100FM/32-2	RF0336-000
0603SFS150F/32-2	RF0337-000
0603SFS150FM/32-2	RF0338-000
0603SFS200F/32-2	RF0339-000
0603SFS200FM/32-2	RF0340-000
0603SFS250F/32-2	RF0341-000
0603SFS250FM/32-2	RF0342-000
0603SFS300F/32-2	RF0343-000
0603SFS300FM/32-2	RF0344-000
0603SFS350F/32-2	RF0345-000
0603SFS350FM/32-2	RF0346-000
0603SFS400F/32-2	RF0347-000
0603SFS400FM/32-2	RF0348-000
0603SFS450F/32-2	RF0349-000
0603SFS450FM/32-2	RF0350-000
0603SFS500F/32-2	RF0351-000
0603SFS500FM/32-2	RF0352-000
PSR-27781	RF2355-000
PSR-28025	RF2356-000
PSR-27893	RF2357-000
PSR-28026	RF2358-000
PSR-28024	RF2359-000
PSR-28027	RF2360-000
1206SFS100F/63-2	D23319-000
1206SFS100FM/63-2	RF0153-000
1206SFS125F/63-2	F11095-000
1206SFS125FM/63-2	RF0154-000
1206SFS150F/63-2	E77174-000
1206SFS150FM/63-2	RF0155-000
1206SFS200F/63-2	A03338-000
1206SFS200FM/63-2	RF0156-000
1206SFS250F/32-2	451674-000
1206SFS250FM/32-2	RF0157-000
1206SFS300F/32-2	799062-000

1206SFS300FM/32-2	RF0158-000
1206SFS350F/32-2	543268-000
1206SFS350FM/32-2	RF0159-000
1206SFS400F/32-2	F09837-000
1206SFS400FM/32-2	RF0160-000
1206SFS450F/32-2	A41268-000
1206SFS450FM/32-2	RF0161-000
1206SFS500F/32-2	E86727-000
1206SFS500FM/32-2	RF0162-000
1206SFS550F/24-2	A52099-000
1206SFS550FM/24-2	RF0163-000
1206SFS600F/24-2	C52564-000
1206SFS600FM/24-2	RF0164-000
1206SFS700F/24-2	C57857-000
1206SFS700FM/24-2	RF0165-000
1206SFS800F/24-2	F88154-000
1206SFS800FM/24-2	RF0166-000
0603SFP100F/32-2	RF0435-000
0603SFP100FM/32-2	RF0436-000
0603SFP150F/32-2	RF0437-000
0603SFP150FM/32-2	RF0438-000
0603SFP200F/32-2	RF0439-000
0603SFP200FM/32-2	RF0441-000
0603SFP250F/32-2	RF0440-000
0603SFP250FM/32-2	RF0442-000
0603SFP300F/32-2	RF0443-000
0603SFP300FM/32-2	RF0444-000
0603SFP350F/32-2	RF0445-000
0603SFP350FM/32-2	RF0446-000
0603SFP400F/32-2	RF0447-000
0603SFP400FM/32-2	RF0448-000
0603SFP450F/32-2	RF0449-000
0603SFP450FM/32-2	RF0452-000
0603SFP500F/32-2	RF0450-000
0603SFP500FM/32-2	RF0451-000
PSR-28486	RF3483-000
0603SFP600F/32-2	RF2971-000
0603SFP600FM/32-2	RF2974-000
1206SFP100F/63-2	RF0453-000
1206SFP100FM/63-2	RF0462-000
1206SFP150F/63-2	RF0454-000
1206SFP150FM/63-2	RF0463-000
1206SFP200F/63-2	RF0455-000
1206SFP200FM/63-2	RF0464-000
1206SFP250F/32-2	RF0456-000
1206SFP250FM/32-2	RF0465-000
1206SFP300F/32-2	RF0457-000

1206SFP300FM/32-2	RF0466-000
1206SFP350F/32-2	RF0458-000
1206SFP350FM/32-2	RF0467-000
1206SFP400F/32-2	RF0459-000
1206SFP400FM/32-2	RF0468-000
1206SFP450F/32-2	RF0460-000
1206SFP450FM/32-2	RF0469-000
1206SFP500F/32-2	RF0461-000
1206SFP500FM/32-2	RF0470-000
1206SFP600F/24-2	RF2855-000
1206SFP600FM/24-2	RF2856-000
1206SFP700F/24-2	RF2857-000
1206SFP700FM/24-2	RF2858-000
1206SFP800F/24-2	RF2859-000
1206SFP800FM/24-2	RF2860-000
0603SFV050F/32-2	RF1558-000
0603SFV050FM/32-2	RF1572-000
0603SFV075F/32-2	RF1559-000
0603SFV075FM/32-2	RF1573-000
0603SFV100F/32-2	RF1560-000
0603SFV100FM/32-2	RF1574-000
0603SFV125F/32-2	RF1561-000
0603SFV125FM/32-2	RF1575-000
0603SFV150F/32-2	RF1562-000
0603SFV150FM/32-2	RF1576-000
0603SFV175F/32-2	RF1563-000
0603SFV175FM/32-2	RF1577-000
0603SFV200F/32-2	RF1564-000
0603SFV200FM/32-2	RF1578-000
0603SFV250F/32-2	RF1565-000
0603SFV250FM/32-2	RF1579-000
0603SFV300F/32-2	RF1566-000
0603SFV300FM/32-2	RF1580-000
0603SFV350F/32-2	RF1567-000
0603SFV350FM/32-2	RF1581-000
0603SFV400F/32-2	RF1568-000
0603SFV400FM/32-2	RF1582-000
0603SFV450F/32-2	RF1569-000
0603SFV450FM/32-2	RF1583-000
0603SFV500F/32-2	RF1570-000
0603SFV500FM/32-2	RF1584-000
1206SFH100F/24-2	RF1585-000
1206SFH100FM/24-2	RF1752-000
1206SFH120F/24-2	RF1586-000
1206SFH120FM/24-2	RF1753-000
1206SFH150F/24-2	RF1587-000
1206SFH150FM/24-2	RF1754-000
1206SFH200F/24-2	RF1588-000



1206SFH200FM/24-2	RF1755-000
1206SFH250F/24-2	RF4207-000
1206SFH250FM/24-2	RF4208-000
1206SFH300F/24-2	RF4209-000
1206SFH300FM/24-2	RF4210-000
PSR-27865-050	RF2537-000
PSR-27865-075	RF2539-000
PSR-27865-100	RF2540-000
PSR-27865-150	RF2541-000
PSR-27865-200	RF2542-000
PSR-27865-250	RF2543-000
PSR-27865-300	RF2544-000
PSR-27865-350	RF2545-000
PSR-27865-400	RF2546-000
PSR-27865-500	RF2547-000
PSR-27865-600	RF2548-000
0603SFC050F/32-2	RF2404-000
0603SFC050FM/32-2	RF2405-000
0603SFC075F/32-2	RF2406-000
0603SFC075FM/32-2	RF2407-000
0603SFC100F/32-2	RF2408-000
0603SFC100FM/32-2	RF2409-000
0603SFC150F/32-2	RF2410-000
0603SFC150FM/32-2	RF2411-000
0603SFC200F/32-2	RF2412-000
0603SFC200FM/32-2	RF2413-000
0603SFC250F/32-2	RF2414-000
0603SFC250FM/32-2	RF2415-000
0603SFC300F/32-2	RF2416-000
0603SFC300FM/32-2	RF2417-000
0603SFC400F/32-2	RF2418-000
0603SFC400FM/32-2	RF2419-000
0603SFC500F/32-2	RF2420-000
0603SFC500FM/32-2	RF2421-000
2410SFV0.50FM/125-2	RF1937-000
2410SFV0.63FM/125-2	RF1938-000
2410SFV0.75FM/125-2	RF1939-000
2410SFV1.00FM/125-2	RF1940-000
2410SFV1.25FM/125-2	RF1941-000
2410SFV1.50FM/125-2	RF1942-000
2410SFV2.00FM/125-2	RF1943-000
2410SFV2.50FM/125-2	RF1944-000
2410SFV3.00FM/125-2	RF1945-000
2410SFV3.15FM/125-2	RF1946-000
2410SFV3.50FM/125-2	RF1947-000
2410SFV4.00FM/125-2	RF1948-000
2410SFV5.00FM/125-2	RF1949-000
2410SFV6.30FM/125-2	RF1950-000

2410SFV7.00FM/125-2	RF1951-000
2410SFV8.00FM/125-2	RF1952-000
2410SFV10.0FM/125-2	RF1953-000
2410SFV12.0FM/065-2	RF1954-000
2410SFV15.0FM/065-2	RF1955-000
2410SFV20.0FM/065-2	RF1956-000
PSR-28101	RF2450-000
PSR-28241-100	RF2735-000
PSR-28241-125	RF2737-000
PSR-28241-150	RF2739-000
PSR-28241-200	RF2741-000
PSR-28241-250	RF2742-000
PSR-28241-300	RF2744-000
PSR-28241-315	RF2746-000
PSR-28241-350	RF2747-000
PSR-28241-400	RF2749-000
PSR-28241-500	RF2751-000
PSR-28241-630	RF4369-000
0603TSFV050FM/65-2	RF4250-000
0603TSFV075FM/65-2	RF4251-000
0603TSFV100FM/65-2	RF4252-000
0603TSFV125FM/65-2	RF4253-000
0603TSFV150FM/65-2	RF4254-000
0603TSFV175FM/35-2	RF4255-000
0603TSFV200FM/35-2	RF4256-000
0603TSFV250FM/35-2	RF4257-000
0603TSFV300FM/35-2	RF4258-000
0603TSFV350FM/35-2	RF4259-000
0603TSFV400FM/35-2	RF4260-000
0603TSFV500FM/35-2	RF4261-000
1206SFV1.50FM/065-2	RF4313-000
1206SFV1.60FM/065-2	RF4314-000
1206SFV2.00FM/065-2	RF4315-000
1206SFV2.50FM/065-2	RF4316-000
1206SFV3.00FM/065-2	RF4317-000
1206SFV3.15FM/065-2	RF4318-000
1206SFV3.50FM/065-2	RF4319-000
1206SFV4.00FM/065-2	RF4320-000
1206SFV5.00FM/032-2	RF4321-000
1206SFV6.30FM/032-2	RF4322-000
1206SFV7.00FM/032-2	RF4323-000
1206SFV8.00FM/032-2	RF4324-000
1206SFV10.0FM/032-2	RF4325-000
1206SFV12.0FM/032-2	RF4326-000
1206SFV15.0FM/032-2	RF4327-000