

02 026528

Quicklock circular connectors, IP67



Quicklock socket with locking latch, IP67, size 28, straight version, with plastic housing and screw clamps


Approvals:




1 of 3 09/2020




02 026528









026528 02 026528 03

Environmental conditions

Temperature range -40 °C/+80 °C

Materials

Insulating body PBT, V-0 according to UL94

Contact bush CuZn, gold-plated

Housing PBT, V-0 according to UL94¹
Guiding element Zn alloy, chrome-plated
Locking Zn alloy, chrome-plated
Cap nut PBT, V-0 according to UL94¹

¹ outdoor sustainable (F1 according to UL 746C)

Mechanical data

Mating cycles 1700
Insertion force ≤ 90 NWithdrawal force ≤ 40 NProtection class 1P67¹

¹ only in locked condition with an appropriate counterpart

Connectable conductors for screw clamp

Section 2.5–16.0 mm²/AWG 14–6

Cable diameter 4.0–11.5 mm

Electrical data (at Tamb 20 °C)

Contact resistance $\leq 5 \text{ m}\Omega$ Rated current50 A (2 poles)
43 A (3 poles)Rated voltage500 V ACRated impulse voltage $\leq 2500 \text{ V}$ Creepage distance $\geq 2 \text{ mm}$ Clearance $\geq 2 \text{ mm}$ Insulation resistance $> 500 \text{ M}\Omega$

Associated products

Counterparts

2 of 3 09/2020



02 026528

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
026528 02	2	2	20
026528 03	3	2	20

Packaging:

in individual plastic bags, in a cardboard box

3 of 3 09/2020