

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2026542021

Status:

Active

Overview:

Pico-EZmate and Pico-EZmate Slim Wire-to-Board Connector Systems

Description:

Pico-EZmate Slim Receptacle Housing, Friction Lock, 2 Circuits, Black

- Documents:
- 3D Model

Application Specification 2026540000-A00 (PDF)
- 3D Model (PDF)

Packaging Specification 2026549200-200 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification 2026540000-000 (PDF)

Product Literature (PDF)

General	
Product Family	Crimp Housings
Series	202654
Application	Signal, Wire-to-Board
Overview	Pico-EZmate and Pico-EZmate Slim Wire-to-Board Connector Systems
Product Name	Pico-EZmate Slim
UPC	191128182041
Physical	
Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	8.160/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.20mm
Pitch - Termination Interface	1.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-25° to +85°C

Material Info

Reference - Drawing Numbers	
Application Specification	2026540000-A00
Packaging Specification	2026549200-200
Product Specification	2026540000-000
Sales Drawing	2026540000-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)4578-DC (25 June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

202654 Series

Mates With

Pico-EZmate Slim Header 202656

Use With

Pico-EZmate Slim Crimp Terminal 2026555000

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION