Home > Products > Sensors > Image Sensors & Processors > Image Sensors > AR0431

# AR0431: CMOS Image Sensor, 4 MP, 1/3.2", Near Infra-Red Enhancement





- »View Material Composition
- » Product Change Notification
- ☐ Mark as Favorite

The ON Semiconductor AR0431 is a stacked 1/3.2-inch BSI CMOS active -pixel digital image sensor with a pixel array of 2312H x 1746V. The AR0431 has been designed for IoT and security cameras. AR0431 can provide high quality imaging for both day and night lighting conditions perfect for security cameras. It has the ability to record at 120 fps delivering slow motion capable video which can use zoom and retain the resolution quality which is perfect for wearable devices.

### **Features**

- 4 MP at 120 frames per second
- High linear full well
- Low power operation and special monitoring mode
- 1/3-inch optical format
- Sensor Synchronization
- Latest stacked pixel technology
- Near Infra-red enhancement

#### **Applications**

• 4 MP CMOS Imaging sensor for consumer and industrial end products.

#### **Benefits**

- Slow Motion video capability
- Great natural dynamic range for challenging lighting conditions
- Power savings, heat savings while fully active or while always on.
- Standard compact sensor size to fit into many IoT type applications
- Allows for multiple camera synchronization for 360 degree cameras or longer range depth solutions
- Compact sensor size and leading color performance
- Save power and cost for using less NIR LEDs

#### **End Products**

Videos (2)

- IoT Camera
- Wearable Camera
- Security Camera
- AR/VR/MR Camera

**Previously Viewed Products** 

Select Product...

**∨** Go

Clear List

# Support

Technical Documentation

Design Resources & Documents

Technical Support

Sales Support

## **Featured Video**

Panel Discussion | The Future of Embedded Vision and Machine Learning

More Videos ...

# **Technical Documentation & Design Resources**

Package Drawings (1)

**Availability & Samples** 

Specifications

Product	Status	Compliance	Description	Package		MSL		Container		Budgetary Price
				Туре	Case Outline	Туре	Temperature	Туре	Qty.	
AR0431CSSC14SMRA0- DP	Active	Pb-free  Halide free	AR0431, Color 14 Deg CRA mPLCC with Protective Film Tray	mPLCC- 48	776AZ	4	260	Tray JEDEC	2400	Contact Sales (
AR0431CSSC14SMRA0- DP1	Active	Pb-free  Halide free	AR0431, Color 14 Deg CRA mPLCC with Protective Film Tray Low MOQ	mPLCC- 48	776AZ	4	260	Tray JEDEC	240	Contact Sales ( Inventory
AR0431CSSC14SMRA0- DR	Active	Pb-free  Halide free	AR0431, Color 14 Deg CRA mPLCC with No Protective Film Tray	mPLCC- 48	776AZ	4	260	Tray JEDEC	2400	Contact Sales ( Inventory
AR0431CSSC14SMRA0- DR1	Active	Pb-free  Halide free	AR0431, Color 14 Deg CRA mPLCC with No Protective Film Tray Low MOQ	mPLCC- 48	776AZ	4	260	Tray JEDEC	240	Contact Sales (

Copyright © 1999-2020 Semiconductor Components Industries, LLC | 沪ICP备18032505号 Do Not Sell My Personal Information | Privacy Policy | Cookie Policy | Terms of Use | Terms of Sale

