

L'espion Mini Spy Digital Camera

- This amazingly cool mini digital camera has replaced the Precision digital camera. The L'espion mini is a little bit smaller than the Precision, and has all the same quality features....



Using the camera is a cinch. A built in retractable Optical Viewfinder allows you to centre subjects and keeps the protruding piece safe when not in use.

There are only two buttons on the camera, the Shutter/Select button and the mode button, which allows you to display the surprising amount of various options. These options included switching resolutions, continuous shutter for recording video, clearing all pictures from the memory, and the always-helpful self-timer.

Easy installation of a single AAA battery, avoids the annoying (and expensive) battery hunt that is often involved with other cameras. Ideal to keep in your pocket for unexpected picture opportunities.

Dimensions 5.5 x 3.8 x 1.5cm

- Electronic element: CMOS Sensor 100K pixels
- Image resolution
- 352 x 288 pixels (CIF)
- 176 x 144 pixels (QCIF)
- Lens: $f = 3.6\text{mm}$ F2.4(54)
- Memory device: built in 2 MB
- Memory capacity: 20 pieces (CIF) ; 80 pieces (Q)
- View-finder: pop up, built-in
- AVI filming mode – 16 secs.
- Shoot mode: single, continuous, automatic
- 10sec self-timer
- Working voltage: AAA 1.5v
- Transmission interface: USB interface Revision 1.1
- Continuous: 10 pieces per second
- Photo software and driver CD
- Operation system: Windows 98 Edition 2/2000/XP
- LiteSync technology (enhances indoor lighting in poor light conditions)
- Image editing software included
- Powered by 1 x AAA battery (included)