

Datasheet

**Thermocouple Terminal Head Type B**



- Thermocouple connection heads
- Cast aluminium, stainless steel or tough ABS plastic
- Side cable entry PG16.
- Pressed steel lid retained by 2 plated screws
- IP66

Head	Material/ Finish	Probe entry	Cable entry	Cable gland	Block fixings (centres)	Max temp.*	Order code
B	Aluminium/	½"BSPP die-casting	PG16	Yes	33mm	100°C	<b>XF-1495-FAR</b>

*\*Max temp limited to temperature rating shown by virtue of sealing ring*