




Datasheet

ANSI Glassfibre Exposed Welded Tip Thermocouples



- Thermocouple type K
- Fast response, welded exposed junction
- 1, 2, 5 & 10-metre-long glassfibre insulated flat pair cable
- Good temperature resistance (not suitable in fluids)
- 1/0.3mm conductors
- Temperature range -60°C to +350°C (short periods up to 400°C)
- Tolerance to ANSI MC96.1 Class 2
- Colour code to ANSI MC96.1
- Ideal for test & development applications

T/C Type	Conductors	Length	+Positive tail wire	-Negative tail wire	Order code
'K'	1/0.3mm	1 metres	Yellow	Red	XF-1503-FAR
'K'	1/0.3mm	2 metres	Yellow	Red	XF-1504-FAR
'K'	1/0.3mm	5 metres	Yellow	Red	XF-1160-FAR
'K'	1/0.3mm	10 metres	Yellow	Red	XF-1508-FAR