

Datasheet

IEC PVC Thermocouple Extension Lead with Miniature Thermocouple Plugs or Sockets



Cable Description

- PVC insulated flat pair construction
- Conductors laid flat PVC insulated with overall PVC sheath
- All round general purpose cable, both waterproof and very flexible
- Thermocouple extension type K, 2 or 5 Metre lengths available
- Conductors 7/0.2mm
- Tolerance Class 2
- Insulation rating -10°C to 105°C
- Colour code (cores & jacket) in accordance with IEC specification

Connector Description

- Ideal for general purpose use
- All contacts are polarised to ensure correct connection
- Colour coded in accordance with IEC specification
- Maximum continuous operating temperature 220°C

Type	Length	Termination	Order Code
K	1m	2 x Miniature Plugs	XF-1528-FAR
K	2m	2 x Miniature Plugs	XF-1529-FAR
K	1m	2 x Miniature Sockets	XF-1530-FAR
K	2m	2 x Miniature Sockets	XF-1531-FAR