

Datasheet

IEC PTFE Exposed Welded Tip Thermocouples with Miniature Thermocouple Plug



- Thermocouple types K, J & T
- Fast response, welded exposed junction 1, 2, 5 or 10 metre lengths available
- Teflon® PTFE insulated twin-twisted lead
- 1/0.2mm conductors
- 'Re-Wireable' miniature flat pin plug
- Temperature range -75°C to +260°C
- Tolerance to IEC 584 Class 1
- Colour code to IEC 584-3
- Ideal for test & development applications

T/C Type	Conductors	Length	Termination	+Positive tail wire	-Negative tail wire	Order Code
'K'	1/0.2mm	2 m	Mini plug	Green	White	XF-1202-FAR
'K'	1/0.2mm	5 m	Mini plug	Green	White	XF-1215-FAR
'K'	1/0.2mm	10 m	Mini plug	Green	White	XF-1216-FAR
'J'	1/0.2mm	1 m	Mini plug	Black	White	XF-1203-FAR
'J'	1/0.2mm	2 m	Mini plug	Black	White	XF-1217-FAR
'J'	1/0.2mm	5 m	Mini plug	Black	White	XF-1218-FAR
'J'	1/0.2mm	10 m	Mini plug	Black	White	XF-1219-FAR
'T'	1/0.2mm	2 m	Mini plug	Brown	White	XF-1220-FAR
'T'	1/0.2mm	5 m	Mini plug	Brown	White	XF-1221-FAR
'T'	1/0.2mm	10m	Mini Plug	Brown	White	XF-1532-FAR