



2000 Watt Hot air gun HG 20-600

- Versatile hot air gun with adjusting wheel for easy, variably adjustment of the temperature
- High-quality ceramic heating, powerful motor and optimum device cooling for long service life
- Wide range of uses: removal of varnish, shaping, crimping, welding and much more
- Ergonomic design and handle with non-slip soft-grip surface provides convenient handling
- Safe stationary application due to large non-slip floor space

Order no.	602066000
EAN code	4061792185906
Air volume	150 / 300 / 500 l / min
Number of air volume levels	3
Air temperature	806001.112 °C
Number of air temperature levels	infinitely variable
Rated input power	2.000 W
Weight (without power cable)	0,62 kg

Scope of delivery

-

metaBOX 145 L, empty (626884000)

Order no. 626884000

EAN 4061792189157



Product may differ from Image

- Intelligent transport and storage system for mobile working
- Extremely robust and break-proof due to the material and design for maximum resilience
- Optimum protection of machine and accessories against dirt and moisture (IP43)
- Fast and easy stacking and coupling of the boxes in all system widths
- One box in the stack can easily be opened without having to decouple it
- A selection of two: Comfortable front handle for carrying the box near you and extra-wide cover handle to carry several stacked-up boxes
- Numerous tailor-made inserts (accessories) for individual order inside the box
- Clever accessories: Roller board and trolley for maximum mobility as well as an adapter plate to secure the boxes in the vehicle
- metaBOX 145 L empty, without inserts

Technical data

Characteristics

Dimensions	496 x 296 x 145 mm / 19.53 x 11.66 x 5.72 "
Case volume	14.1 l
Max. load cover	125 kg / 275.6 lbs
Weight	1.85 kg / 4.1 lbs
Material	ABS