

## **OA825EC XC Series**



## EC Fan Universal Voltage 80x25mm (3.15" x 0.98")







40

48

Frame	PBT UL94V0- Plastic
Impeller	PBT UL94V0- Plastic
Connection	Wire Leads
Motor	AC-DC Energy Saving, Electronically Protected
Bearing System	Dual Ball Bearings
Dielectric Strength	1500VAC/min

Operating Temperature -10C ~ +70C

Storage Temperature -40C ~ +75C

<u>Life Expectancy</u> 70,000 hours (L10 at 40C)

Weight: ~ 0.17 lbs

m0

Static Pressure ("H<sub>2</sub>O) 0.16 0.12 0.08 0.04 24 16 32 Airflow (CFM)

0.20

Part Number	OA825EC-UR-1WBXC
Rated Voltage	110/220 VAC
Voltage Range	85 ~ 265
Rated Input	6 ~ 4 (2.2)W
Rated Speed (RPM)	3000
Airflow (CFM)	40.2
Noise Level (dB)	38
Max. Static Pressure	0.2"H <sub>2</sub> O







