

OA938EC XC Series



EC Fan Universal Voltage 92x38mm (3.62" x 1.50")







Frame	PBT UL94V0- Plastic
Impeller	PBT UL94V0- Plastic
Connection	Wire Leads
Motor	AC-DC Energy Saving, Electronically Protected
Bearing System	Dual Ball Bearings
Dielectric Strength	1500VAC/min


Operating Temperature -10C ~ +70C

Storage Temperature -40C ~ +75C

Life Expectancy 70,000 hours (L10 at 40C)

Weight: ~ 0.42 lbs

m0



Part Number	OA938EC-UR-1WBXC
Rated Voltage	110/220 VAC
Voltage Range	85 ~ 265
Rated Input	11 ~ 9 (7.9)W
Rated Speed (RPM)	4200
Airflow (CFM)	88
Noise Level (dB)	52
Max. Static Pressure	0.5"H ₂ O







