
OA125EC Series



EC Fan Universal Voltage 120x25mm (4.72" x 0.98")





Frame	PBT UL94V0- Plastic
Impeller	PBT UL94V0- Plastic
Connection	Wire Leads
Motor	AC-DC Energy Saving, Electronically Protected
Bearing System	Dual Ball Bearings
Dielectric Strength	1500VAC/min


Operating Temperature -10C ~ +70C

Storage Temperature -40C ~ +75C

Life Expectancy 70,000 hours (L10 at 40C)

Weight: ~ 0.39 lbs

m0



Part Number	OA125EC-UR-1WB
Rated Voltage	110/220 VAC
Voltage Range	85 ~ 265
Rated Input	8 ~ 6 (2.8)W
Rated Speed (RPM)	3000
Airflow (CFM)	80
Noise Level (dB)	49
Max. Static Pressure	0.21"H ₂ O







