
## OA9232EC Series




## EC Fan Universal Voltage 92x32mm (3.62" x 1.26")





| Frame               | PBT UL94V0- Plastic                              | Operating Temperature<br>-10C ~ +70C         | 0.25   |
|---------------------|--|--|--|
| Impeller            | PBT UL94V0- Plastic                              | <u>Storage Temperature</u><br>-40C ~ +75C    | Ô <sup>, 0.20</sup><br>₽ 0.15                      |
| Connection          | Wire Leads                                       | Life Expectancy<br>70,000 hours (L10 at 40C) |  |
| Motor               | AC-DC Energy Saving,<br>Electronically Protected | Weight: ~ 0.31 lbs                           | 0.10<br>   |
| Bearing System      | Dual Ball Bearings                               |  | <b>5</b> 0.05<br><b>5</b> 0<br>0 10 20 30 40 50 60 |
| Dielectric Strength | 1500VAC/min                                      | m0   | Airflow (CFM)                                      |

| Part Number          | OA9232EC-UR-1WB       |  |
|----------------------|-----------------------|--|
| Rated Voltage        | 110/220 VAC           |  |
| Voltage Range        | 85 ~ 265              |  |
| Rated Input          | 8 ~ 6 (2.1)W          |  |
| Rated Speed (RPM)    | 3000                  |  |
| Airflow (CFM)        | 58                    |  |
| Noise Level (dB)     | 43                    |  |
| Max. Static Pressure | 0.23″H <sub>2</sub> O |  |



Δ

RoHS