
OA92EC XC Series



EC Fan Universal Voltage 92x25mm (3.62" x 0.98")





Frame	PBT UL94V0- Plastic
Impeller	PBT UL94V0- Plastic
Connection	Wire Leads
Motor	AC-DC Energy Saving, Electronically Protected
Bearing System	Dual Ball Bearings
Dielectric Strength	1500VAC/min


Operating Temperature -10C ~ +70C

Storage Temperature -40C ~ +75C

Life Expectancy 70,000 hours (L10 at 40C)

Weight: ~ 0.22 lbs

m0



Part Number	OA92EC-UR-1WBXC
Rated Voltage	110/220 VAC
Voltage Range	85 ~ 265
Rated Input	8 ~ 6 (4.0)W
Rated Speed (RPM)	2600
Airflow (CFM)	56
Noise Level (dB)	35
Max. Static Pressure	0.16"H ₂ O







