



2622NB

Product no.: 2622NB


Side cutter – pointed relieved head



This is the narrowest head shape.



The underside is relieved and facilitates optimum access even to extremely hard-to-reach areas.



source images




The Perfect Cut - Strong, sharp and precise, every time


The Weller Erem Series 2600 MagicSense is a range of medium-sized precision cutters that have a resistant tungsten carbide edged cutting blades. They are made for cutting hard and tough wires, e.g. piano wire, nickel and diode leads. These cutters are manufactured from high grade tool steel. The precision cutters have a nonreflecting surface, are ESD safe and resharpenable.

Type	Type of Cut	Cutting Capacity
------	-------------	------------------

Series 2400 MagicSense

mm	0,03	0,1	0,2	0,3	0,4	0,5	0,6	0,7	0,8	0,9	1,0	1,1	1,2	1,3	1,4	1,5	1,6	1,7	1,8	1,9	2,0
Inch	.0001	.003	.007	.011	.015	.019	.023	.027	.031	.035	.039	.043	.047	.051	.055	.059	.062	.066	.070	.074	.078

	2412E	 Semi Flush	
	2422E	 Flush	
	2432E	 Super Full Flush	
	2477E	 Flush	
	2403E	 Flush	
	2404E	 Flush	
	2482E	 Flush	
	2475E	 Flush	
	2470E	 Flush	
	2476TX2	 Flush / Carbide	





Technical Data

Length mm	125
Length of cutting edges mm	6
Head width mm	9
Head thickness mm	6
Head length mm	16
Max. cutting capability – hard wire mm	---
Weight in oz	2.497
Length of cutting edges Inches	0.236
Head width Inches	0.354
Head thickness Inches	0.236
Head length Inches	0.630
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	Ø 0,6
Max. cutting capability – copper wire mm	Ø 0,8
Length inches	4.921
Weight in g	70.8
Erem applications	Microelectronic