

SCREWTY M12 KO O. SD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The Screwty® attachment is suitable for M12 round plug-in connectors, with an outside dimension of the knurled nut of 14.5 ± 0.3 mm. The tightening torque is 0.8-1.2 Nm.

General ordering data

Type	SCREWTY M12 KO O. SD
Order No.	1900100000
Version	Tools, Cable gland tool for moulded M12 lines
GTIN (EAN)	4032248409952
Qty.	1 pc(s).

Creation date September 7, 2020 10:59:29 AM CEST

Catalogue status 05.09.2020 / We reserve the right to make technical changes.

SCREWTY M12 KO O. SD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight 16 g

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
eClass 9.0	21-04-50-03	eClass 9.1	21-01-90-90
eClass 10.0	21-04-50-03		

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN CAT 8 SAI 15/16 EN FL FIELDWIRING EN
Engineering Data	STEP