



CSB4-M1251M1250

► SPLITTERS



Splitter M128M 5- Pin Euro to M12F 5- pin Euro,
M12F 5- pin Euro, M12F 5- pin Euro and M12F 5- pin
Euro connectors

Black PVC 22-5 AWG Trunk cordset, Straight
Connectors

Trunk: 0.3 m; Branches: 0.0 m

Part Number: 808663

SPECIFICATIONS

Number of Contacts	25
Number of Connectors	5
Cable Jacket Material	PVC
Connector Body Material/Color	PUR Black
Outside Cable Diameter (mm)	5.6
Cordset Length (m)	0.33
Trunk Length (m)	0.3
Shield/No Shield	No Shield
Coupling Material/Color	Nickel Plated Brass
Maximum Temp. (°C)	105
Current Rating (A)	4.0

Minimum Temp. (°C)	-40
Voltage Rating (V)	250 V ac/dc
Primary Connector Type	EURO
Primary Coupling Method	M12 Single Key
Primary Gender	Male
Primary Orientation	Straight
Primary Number of Conductors	5
Primary AWG	22
Splitter Branches: Connector Type	M12F, M12F, M12F, M12F
Splitter Branches: Coupling Method	M12 Single Key, M12 Single Key, M12 Single Key, M12 Single Key
Splitter Branches: Orientation	Straight, Straight, Straight, Straight
Splitter Branches: Number of Conductors	5, 5, 5, 5
Splitter Branches: AWG	22, 22, 22, 22
Splitter Function	Parallel
Feature: Hazardous Area	No
Oil/Grease Resistant	No



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America

