



Creating Safe Work Solutions During COVID-19

WLS15HCWW1200LS24QP

► WLS15 LOW PROFILE, LOW POWER LED STRIP LIGHT



WLS15 High Intensity Light Strip; Light Diffuse Window; Length: 1200 mm

Voltage: 24 V dc; Environmental Rating: IP66; IP67

Color: WW; Cascadable

Euro 4-pin 150 mm (6 in) PVC Pigtail

Part Number: 809911

CERTIFICATIONS



SPECIFICATIONS

Cable Length (m)	2
Housing Style	Linear Strip
Primary Housing Material	Polycarbonate
Illumination	Yes
Mounting Thread	No Thread
Color Input Control	Individual (One wire/color, same number of colors as input wires)
Number of Colors / Segments	1
Product Size (mm)	15

Chat with an Expert

Color Technology	Standard LED
Color Option 1	White
Connection	Pigtail QD
Quick Disconnect Type	M12 (Euro)
Lumens Color 1	2800
Color 1 - Wavelength/Color Temp/Coordinates	3000K (Warm)
Max Current Color (mA)	1440
Dimming Option	High-Low-Off
Number of Input Pins/Conductors	4
Supply Voltage	24 V dc
Illuminated Length (LxWxH mm)	1126.4
Physical Dimensions (LxWxH or DxH mm)	1200.0 x 30.6 x 15.5
Environmental Rating	IP66; IP67
Max Op. Temperature (°C)	50
Min Op. Temperature (°C)	-40
Storage Temp (°C)	-40 to 70
Primary Window Material	Polycarbonate Diffused
Secondary Material	Polyamide
Feature: Hazardous Area	No
Feature: Audible	No
Feature: Cascade	Yes
Feature: Chemical Resistant	No
IO Link	No
Modbus RTU	No
Wireless	No
USB	No

 Chat with an Expert

Pro-Editor Compatible	No
-----------------------	----

COMPATIBLE PRODUCTS

BRACKET

LMBWLS15	Bracket: For Use with WLS15 Mounting Clip Kit Contains 3 Brackets
LMBWLS15-150S	Bracket: For Use with WLS15 150 Degree Rotation Set of Two Stainless Steel
LMBWLS15MAG	Bracket: For Use with WLS15 Magnetic Mounting Kit Set of Two Up to 16 lb Pull

DOUBLE-ENDED CORDSETS

MQDEC-401SS	Euro-style Quick Disconnect Cable Double-ended 4-pin Male Connector Straight 4-pin Female Connector Straight 0.3 m Length Chrome plated brass coupling nut
MQDEC-403SS	Euro-style Quick Disconnect Cable Double-ended 4-pin Male Connector Straight 4-pin Female Connector Straight 0.91 m Length Chrome plated brass coupling nut
MQDEC-406SS	Euro-style Quick Disconnect Cable 4-pin Straight Connector 2 m (6.5 ft) Length Double Ended With 1 Female & 1 Male Connector
MQDEC-412SS	Euro-style Quick Disconnect Cable Double-ended 4-pin Male Connector Straight 4-pin Female Connector Straight 3.7 m Length Chrome plated brass coupling nut
MQDEC-420SS	Euro-style Quick Disconnect Cable Double-ended 4-pin Male Connector Straight 4-pin Female Connector Straight 6.1 m Length Chrome plated brass coupling nut
MQDEC-430SS	Euro-style Quick Disconnect Cable Double-ended 4-pin Male Connector Straight 4-pin Female Connector Straight 9.1 m Length Chrome plated brass coupling nut



Chat with an Expert

MQDEC-450SS

Euro-style Quick Disconnect Cable
Double-ended 4-pin Male Connector Straight
4-pin Female Connector Straight 15 m Length
Chrome plated brass coupling nut

SINGLE-ENDED CORDSETS**MQDC-406**

Euro-style Quick Disconnect Cable
4-Pin Straight Connector
2 m (6.5 ft) in Length
Nickel-plated Brass Coupling Nut

MQDC-406RA

Euro-Style Quick Disconnect Cable
4-Pin Right-Angle Connector
2 m (6.5 ft) in Length
Nickel-plated brass coupling nut

MQDC-415

Euro-style Quick Disconnect Cable
4-Pin Straight Connector
5 m (15 ft) in Length
Nickel-plated Brass Coupling Nut.

MQDC-415RA

Euro-Style Quick Disconnect Cable
4-Pin Right-Angle Connector
5 m (15 ft) in Length
Nickel-plated brass coupling nut

MQDC-430

Euro-style Quick Disconnect Cable
4-Pin Straight Connector
9 m (30 ft) in Length
Nickel-plated Brass Coupling Nut

MQDC-430RA

Euro-Style Quick Disconnect Cable
4-Pin Right-Angle Connector
9 m (30 ft) in Length
Nickel-plated brass coupling nut

MQDC-450

Euro-Style Quick Disconnect Cable
4-Pin Straight Connector
15 m (50 ft) in Length
Nickel-plated Brass Coupling Nut

MQDC-450RA

Euro-Style Quick Disconnect Cable
4-Pin Right-Angle Connector
15 m (50 ft) in Length
Nickel-plated brass coupling nut

MISCELLANEOUS**LMBWLS15TD**

Two strips of 3M Dual Lock adhesive

 Chat with an Expert

	LMBWLS15TF Two strips of double sided foam urethane tape
--	---

LC65 LED DIMMING MODULE

	LC65P2T LED Dimmer Module; 2 -Wire
Pulse Width Modulation
12-30 V dc; 4 Amps
Terminal Connection
--	--

	PSD-24-4 DC Power Supply - Desktop Style
Input: 90-264 V ac 50/60 Hz: 1.8 m (6 ft) US Style outlet plug
Output: 24 V dc 4 A: 2 m (6.5 ft) Euro 4-pin Connector
UL Listed Class 2
--	--



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America

 Chat with an Expert