



### CAT III Multimeter Test Lead Set

Durable nylon carry case containing red and black test probes. 4mm banana plugs directly behind the probe tips, allow simple connection to standard 4mm test sockets. Features snap-on safety tips for Cat III rating and 4mm sockets for connection to standard 4mm test leads.

Two insulated right angle plunger hook clips for easy attachment to wires and component legs. The built-in 4mm sockets allow connection to test leads having shrouded, unshrouded, or retractable 4mm banana plugs.

Also included, a pair of 4mm plug-on, fully insulated 1000V Cat III and 600V Cat IV safety rated Alligator clips, facilitating hand free test connections.

Completing the kit, a pair of 1 metre flexible PVC jacketed red and black test leads, fitted with one right angle and one straight shrouded 4mm banana plugs. Rated 1000V safety Cat III.

The durable nylon carry case protects the test kit from damage, tangles and snagging.

Fully compatible with all major Digital Multimeter brand instruments fitted with standard 4mm sockets.

Carry Case	Durable Nylon Pouch, Velcro Fastening
BU-26103	Test Probes with 4mm Banana Plug
Safety Category	1000V CAT III (with safety tips)
Current Rating	20A
BU-20431	Insulated Right Angle Plunger Hooks
Safety Category	1000V CAT III
Current Rating	15A
BU-126	Fully Insulated Alligator Clips
Safety Category	1000V CAT III / 600V CAT IV
Current Rating	10A
BU-6162-N-39	4mm PVC Jacketed Test Leads
Safety Category	1000V CAT III
Current Rating	20A
Length	1 Metre
Approvals	 