



Snap Fit Bushing - Panel Thickness Range 0.8 - 6.4 mm | 0.031 - 0.250 in ; Approximate Cable Holding Diameter 62.7 mm | 2.470 in

Item code: 22MP30039

Nylon Open Snap Fit Bushing holds up to 62.7 mm | 2.470 in diameter bundles while creating a smooth, insulated opening. The split design easily snaps into 76.2 mm | 3.000 in holes in panels up to 6.4 mm | 0.250 in thick.

Specifications

Approximate Cable Holding Diameter	2.470 in
Compatible Hole Diameter	3.000 in
Head Diameter	3.160 in
Inside Diameter	2.470 in
Maximum Operating Temperature	185 °F
Maximum Panel Thickness	0.250 in
Minimum Operating Temperature	-40 °F
Minimum Panel Thickness	0.031 in
Operating Temperature Range	-40 - 185 °F
Overall Height	0.720 in
Panel Thickness Range	0.031 - 0.250 in
Bushing Type	Closed
Color	Black
Full Material	Nylon 6
Material	Nylon
Material Flammability Standard	UL94 V-2
Open/Closed	Open
Special Features	Heat-Stabilized