



Part Number: NEB-POC-0005



### **Professional, Rechargeable Penlight. IP67 Dust & Waterproof.**

The NEBO INSPECTOR RC is a powerful, professional 360 lumen rechargeable, waterproof (IP67) penlight. The INSPECTOR RC features FLEX-POWER and is equipped with a removable steel clip, 4x zoom and 3 light modes (high, low, strobe) and Soft-Touch Technology, which provides momentary operation when the light is off, with the slight touch of the button.

## Description

The NEBO INSPECTOR RC is a powerful, professional 360 lumen rechargeable, waterproof (IP67) penlight.

The INSPECTOR RC features FLEX-POWER and is equipped with a removable steel clip, 4x zoom and 3 light modes (high, low, strobe) and Soft-Touch Technology, which provides momentary operation when the light is off, with the slight touch of the button.

### **LIGHT MODES (RC Battery)**

- High (360 lumens) - 1 hours / 125 meters
- Low (120 lumens) - 3 hours / 70 meters
- Strobe (360 lumens) - 25 minutes / 125 meters

### **LIGHT MODES (AAA batteries)**

- High (100 lumens) - 1 hours / 90 meters
- Low (30 lumens) - 4 hours / 50 meters
- Strobe (100 lumens) - 25 minutes / 90 meters

### **DESIGN**

- Anodised aircraft-grade aluminium
- Impact-resistant and waterproof (IP67)
- 4x adjustable zoom
- Detachable steel belt/pocket clip

### **OPERATION**

- Rear-positioned, ON/OFF button
- Soft Touch Button for fast deployment

### **BATTERIES**

- Powered by either 2 AAA batteries or 1 10850 750mAh rechargeable battery (included)

### **ACCESSORIES**

- Micro USB to USB charging cable (included)

- Powered by either 2 AAA batteries or 1 10850 750mAh rechargeable battery (included)

### **SPECS**

- Height : 160mm (compact) 165mm (extended)
- Diameter: 18mm
- Weight: 62 grams