

Cordless hot air tool - Professional Line

mobile heat MH5

UK including rechargeable 5.5Ah battery and charger
EAN 4007841 068356



Function description

Mobil. Fast. Powerful. Mobile heat MH5, the 18 V cordless hot air tool with flexible setting options. Temperatures from 50°C to 500°C, with 6 airflow rates (up to 300 l/min) for any application. Ready for use in less than 4 seconds. LCD display for a perfect overview and settings. 4 preset application-specific programmes – can be changed at any time. The security lock button and LED illumination on the base of the tool ensure safe working. Compatible with all push-on standard nozzles from STEINEL. Including case, 5.5 Ah CAS rechargeable battery and charger.

Technical specifications

Temperature	50 – 500 °C
Airflow rate	300 l/min
Motor, type	Brush motor
Function, life expectancy, motor	500 h
Temperature setting	in 10°C steps by joystick
Temperature display	LCD display
Power supply, detail	Rechargeable lithium-ion battery
Heating element	Ceramic heating element
Loc function	No
Residual heat indicator	No
Function, hanger	Yes

Replaceable heating element	No
Thermal cut-out	Yes
Thermostat	No
Dimensions (L x W x H)	225 x 72 x 204 mm
Rechargeable battery voltage	18 V
Mains power supply	18 V
Model	Case
PU1, net weight	0,66 kg
Manufacturer's Warranty	1 year
PU1, EAN	4007841068356

Accessories

EAN 4007841 068257	Spare CAS battery 18V LiHD
EAN 4007841 068240	Spare CAS battery 18V LiHD
EAN 4007841 068349	CAS Fast Charger ASC 145
EAN 4007841 075569	12-piece hot-air accessory kit
EAN 4007841 075811	Shrink tubing kit