EAO – Your Expert Partner for **Human Machine Interfaces**

82-6151.2124.B001 - Illuminated pushbutton 22 mm stainless-steel On/Off Symbol

82-6151.2124.B001 - Illuminated pushbutton 22 mm stainless-steel, maintained, On/Off Symbol



Mounting

Mounting cut-out Ø 22,3 mm Design flush

Front

Front dimension Ø 25 mm
Front shape round
Front ring shape flush

Front bezel material Stainless steel

Other Attributes

Operating voltage (LED) 24 V AC/DC Weight 0,018 kg
Operation current (LED) 7 mA

Operating-/Indication part

Lens optics opaque
Lens material Stainless steel
Lens profile flat
Lens illumination illuminative
Lens colour Stainless steel

IP-Rating

Front protection IP65, IP67

Connection Method

Terminal Solder 2.8 x 0.5 mm

Actuator

Switching action Maintained

Switching element

Switching current 3 A
Contact material Silver
Contacts 1 C

Switching system Snap-action switching element

Switching voltage 240 V AC/DC

Illumination

Illumination Ring with blue LED


Function

Illuminated pushbutton


EAO – Your Expert Partner for **Human Machine Interfaces**

82-6151.2124.B001 - Illuminated pushbutton 22 mm stainless-steel On/Off Symbol


Dimensions




Mounting cut-outs



Wiring diagram



Component layout



Legend

Switching action: C = Maintained Contacts: C = Changeover