

Pushbutton, 18.2 mm, screw terminal, momentary contact function, 1 NC + 1 NO, bezel black



fields of application

- > Mechanical and system engineering
- > Model construction
- > Home technology



description

Pushbutton with mounting hole diameter 18.2 mm, non-illuminated, 250 V / 4 A

technical data

> general

illuminated	No
Bezel color	black
Collar shape	round
Operating temperature, min.	-25 °C
Operating temperature, max.	85 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	90 °C
Packaging	Box
Packaging unit	100 pcs.
net weight	16 g
standard delivery time	3 weeks
Operating life	50,000 Cycles
Degree of protection, front side,	IP40
according to DIN EN 60529	IP65
	IP65 with sealing cap
RoHS compliant	Yes
REACH compliant	Yes
MOQ order	100

direct links

- > [RAFI eCatalog](#)

> mounting diameters

Mounting hole	18.2 mm
Mounting depth	34 mm
Installation height	10.5 mm
Outside dimension, width	22 mm
> mechanical data	
Actuation function	momentary contact function
Operating force, min.	9.5 N
Operating travel, max.	5 mm
Contact function	1 NC + 1 NO
Contact system	Bridge-sliding contact
Contact material	Silver
Fixing	Threaded ring
Terminal on the rear	Screw terminal
> electrical data	
Rated voltage, max.	250 V
Rated current, max.	2 A