



1500
LUMEN



2 1/2 - 10H
RUNTIME



48M
RANGE



IP65/IK07
IP RATING

HX1500R - COMPACT DUAL LED WORK LIGHT

- 1500 lumen 15W white COB LED, 6500K
- Additional 500 lumen 5W SMD LED spot beam, 6500K
- Ultra tough nylon-polymer and aluminium construction
- 180° rotating stand with super strong magnetic base
- IP65 dust & water resistant
- IK07 shock proof - 2m drop resistant
- Operating temperature -20°C to +50°C
- High power 5200mAh lithium battery
- Battery level and charging indicator lights
- Faster 2A USB Type-C charging - 4 hours charge time
- 1m high quality USB Type-C charging cable (included)

BATTERY 3.7v 5200mAh Li-ion Rechargeable Battery
WEIGHT 400g
DIMENSION 116 x 101 x 41.5mm



BATTERY & CHARGE INDICATORS

USB
TYPE-C

