
### Rectangular Power Connectors



The Bulgin Rectangular Power Connector range offers a reliable, rugged solution for cable to cable applications in harsh environments with its environmentally sealed range of products.

The series has a male and female option, as well as modifications such as enhanced seal retention, protective end caps, shrink boot adapters, welded flange, terminating resistors and a Y-Type connector for the automotive industry.



PX0100


6



Rectangular Power Connector Male



- O 2, 3, 4, 6, 8 & 12 poles
- Male housing
- Socket contacts
- Available in Grey and Black
- Additional options available



Part Number	Poles	Key	Termination	Colour	Additional
PX0100S02BK	2	-	Crimp	Black	-
PX0100S02GY	2	-	Crimp	Grey	-
PX0100S03BK	3	-	Crimp	Black	-
PX0100S03GY	3	-	Crimp	Grey	-
PX0100S04BK	4	-	Crimp	Black	-

Crimp

Crimp

Crimp

Crimp

Crimp

Rectangular Power Connector Male - ESR

PX0100S04GY

PX0100S06BK


PX0100S06GY

PX0100S08AGY

PX0100S12AGY



- O 2 poles
- Male housing
- Enhanced seal retention
- Socket contacts
- Available in Black
- Additional options available



Grey

Black

Grey

Grey

Grey

Part Number	Poles	Key	Termination	Colour	Additional	
PX0102S02BK	2	-	Crimp	Black	ESR	


Rectangular Power Connector Male - ESR & PEC



PX0103

PX0102

- O 2 poles
- Male housing
- Enhanced seal retention & protective end cap
- Socket contacts
- Available in Grey
- O Additional options available




Part Number	Poles	Key	Termination	Colour	Additional
PX0103S02GY	2	-	Crimp	Grey	ESR & PEC

Rectangular Power Connector Male - ESR & SBA



PX0104

- O 2 poles
- Male housing
- Enhanced seal retention & shrink boot adapter
- Socket contacts
- Available in Black
- Additional options available




Part Number	Poles	Key	Termination	Colour	Additional
PX0104S02BK	2	-	Crimp	Black	ESR & SBA



Rectangular Power Connector Male -



- O 2, 3, 4, 6, 8 & 12 poles
- Male housing
- Protective end cap
- Socket contacts
- Available in Grey and Black
- Additional options available



PX0105


Part Number	Poles	Key	Termination	Colour	Additional
PX0105S02BK	2	-	Crimp	Black	PEC
PX0105S02GY	2	-	Crimp	Grey	PEC
PX0105S03BK	3	-	Crimp	Black	PEC
PX0105S03GY	3	-	Crimp	Grey	PEC
PX0105S04BK	4	-	Crimp	Black	PEC
PX0105S04GY	4	-	Crimp	Grey	PEC
PX0105S06BK	6	-	Crimp	Black	PEC
PX0105S06GY	6	-	Crimp	Grey	PEC
PX0105S08ABK	8	Α	Crimp	Black	PEC
PX0105S08AGY	8	Α	Crimp	Grey	PEC
PX0105S12AGY	12	Α	Crimp	Grey	PEC
PX0105S12ABK	12	Α	Crimp	Black	PEC

Rectangular Power Connector Male -



PX0108

- O 2, 3, 4 poles
- Male housing
- Shrink boot adapter
- Socket contacts
- Available in Grey
- Additional options available




Part Number	Poles	Key	Termination	Colour	Additional
PX0108S02GY PX0108S03GY	2 3	-	Crimp Crimp	Grey Grey	SBA SBA
PX0108S04GY	4	-	Crimp	Grey	SBA

Rectangular Power Connector Male - TFR



- PX0110
- O 3 poles
- Male housing
- Terminating resistor
- Socket contacts
- Available in Grey
- Additional options available



Part Number	Poles	Key	Termination	Colour	Additional	
PX0110S03GY	3	_	Crimp	Grev	TER	


PX0101



Rectangular Power Connectors Female



- O 2, 3, 4, 6, 8 & 12 poles
- Female Housing
- Wedge-locks included
- Pin contacts
- O Available in Grey and Black
- Additional options available




Part Number	Poles	Key	Termination	Colour	Additional
PX0101P02BK	2	_	Crimp	Black	-
PX0101P02GY	2	_	Crimp	Grev	-
PX0101P03BK	3	-	Crimp	Black	-
PX0101P03GY	3	_	Crimp	Grev	-
PX0101P04BK	4	-	Crimp	Black	-
PX0101P04GY	4	_	Crimp	Grev	-
PX0101P06BK	6	-	Crimp	Black	-
PX0101P06GY	6	-	Crimp	Grey	-
PX0101P08ABK	8	Α	Crimp	Black	-
PX0101P08AGY	8	Α	Crimp	Grey	-
PX0101P12ABK	12	Α	Crimp	Black	-
PX0101P12AGY	12	Α	Crimp	Grey	-

Rectangular Power Connectors Female -

- REC

PX0106

- Q 2, 3, 4, 6, 8 & 12 poles
- Female Housing
- Wedge-locks included
- Pin contacts
- Available in Grey and Black
- Additional options available



Part Number	Poles	Key	Termination	Colour	Additional
PX0106P02BK	2	-	Crimp	Black	PEC
PX0106P02GY	2	-	Crimp	Grey	PEC
PX0106P03BK	3	-	Crimp	Black	PEC
PX0106P03GY	3	-	Crimp	Grey	PEC
PX0106P04BK	4	-	Crimp	Black	PEC
PX0106P04GY	4	-	Crimp	Grey	PEC
PX0106P06BK	6	-	Crimp	Black	PEC
PX0106P06GY	6	-	Crimp	Grey	PEC
PX0106P08ABK	8	Α	Crimp	Black	PEC
PX0106P08AGY	8	Α	Crimp	Grey	PEC
PX0106P12ABK	12	Α	Crimp	Black	PEC
PX0106P12AGY	12	Α	Crimp	Grey	PEC

Rectangular Power Connector Male -



Ų

PX0107

- O 3 poles
- Male housing
- Protective end cap
- Socket contacts
- Available in Grey
- O Additional options available



Part Number	Poles	Key	Termination	Colour	Additional
PX0107P03GY	3	-	Crimp	Grey	PEC & SBA




Rectangular Power Connector Male -



PX0109

- O 2, 3 & 4 poles
- Male housing
- Protective end cap
- Socket contacts
- Available in Grey and Black
- Additional options available



Part Number	Poles	Key	Termination	Colour	Additional
PX0109P02BK	2	-	Crimp	Black	SBA
PX0109P02GY	2	-	Crimp	Grey	SBA
PX0109P03BK	3	-	Crimp	Black	SBA
PX0109P04GY	4	-	Crimp	Grey	SBA

Rectangular Power Connector Male -



PX0111

- O 3, 3, 4, 8 & 12 poles
- Male housing
- Protective end cap
- Socket contacts
- Available in Grey
- Additional options available




Part Number	Poles	Key	Termination	Colour	Additional
PX0111P03GY	3	-	Crimp	Grey	TER

Rectangular Power Connector Male - WFL



PX0112

- 3, 3, 4, 8 & 12 poles
- Male housing
- Protective end cap
- Socket contacts
- Available in Grey
- Additional options available



Part Number	Poles	Key	Termination	Colour	Additional
PX0112P02GY	2	-	Crimp	Grey	WFL
PX0112P03GY	3	-	Crimp	Grey	WFL
PX0112P04GY	4	-	Crimp	Grey	WFL
PX0112P08AGY	8	Α	Crimp	Grey	WFL
PX0112P12AGY	12	Α	Crimp	Grey	WFL

Rectangular Power Connector Male -



PX0113

- O 3 poles
- Male housing
- Protective end cap
- Socket contacts
- Available in Grey
- Additional options available



Part Number	Poles	Key	Termination	Colour	Additional
PX0113P03GY	3	-	Crimp	Grey	YTY







- O Crimp Pin & Sockets
- O Choice of Gold and Nickel Plated
- Green Stripe available

Part Number	Plating	AWG	Туре	Pin / Socket	Additional
SA1000/G	Nickel Plating	14	Solid	Pin	Green Stripe
SA1001/G	Nickel Plating	14	Solid	Socket	Green Stripe
SA1002/G	Nickel Plating	16 - 20	Solid	Pin	Green Stripe
SA1003/G	Nickel Plating	16 - 20	Solid	Socket	Green Stripe
SA1000	Nickel Plating	14	Solid	Pin	-
SA1001	Nickel Plating	14	Solid	Socket	_
SA1002	Nickel Plating	16 - 20	Solid	Pin	_
SA1003	Nickel Plating	16 - 20	Solid	Socket	_
SA1004	Nickel Plating	16 - 20	Stamped	Pin	Bandolier
SA1005	Nickel Plating	16 - 20	Stamped	Socket	Bandolier
SA1006	Nickel Plating	14, 16, 18	Stamped	Pin	Bandolier
SA1007	Nickel Plating	14, 16, 18	Stamped	Socket	Bandolier
SA1008	Gold Plating	14, 16, 18	Stamped	Pin	Bandolier
SA1009	Gold Plating	14, 16, 18	Stamped	Socket	Bandolier

Wedgelocks



- O Pin & Sockets available
- O 2, 3, 4, 6, 8 & 12 Pole

\* Wedgelocks are sold separately and are required for confirmation of alignment of contact. Please refer to the chart above to determine part required: e.g. WLP02 is required for 2 pole female housings

WLP12

Part Number	Contacts	Pin / Socket	Additional
WLP02	02	Pin	-
WLS02	02	Socket	-
WLS02ENS	02	Socket	Enhanced Seal
WLP03	03	Pin	-
WLS03	03	Socket	-
WLP04	04	Pin	-
WLS04	04	Socket	-
WLP06	06	Pin	-
WLS06	06	Socket	-
WLP08	08	Pin	-
WLS08	08	Socket	-
WLP12	12	Pin	-
WLS12	12	Socket	-

### Tooling



- O Crimp tooling available
- Probe extraction tool

### Part Number Additional

10000 10001 10002 Crimping tool for heavy duty Rectangular Connectors (series coming soon)
Probe extraction tool
Crimping tool for Rectangular Connectors



### **Electrical:**

No Poles: 2, 3, 4, 6, 8 & 12

Current Rating: 13A Voltage Rating: 250V DC

>1000MΩ (@ 500V DC) Insulation Resistance:

Dielectric Strength: <2mA @ 15V AC

Operating

**Material** 

Temperature Range: -40°C to +120°C

Body Mouldings: Polybutylene Terephthalate, Polyamide

Glass Fiber

Contacts: Copper Alloy Nickel Plated, Copper Alloy

Gold Plated

Rubber Seal: Silicone Rubber RoHS Compliant

Sealing:

**Mechanical:** 

Contact Accommodation: 14 - 20 AWG 2.5-0.35 mm<sup>2</sup>

IP68

Termination: Crimp terminals

Contact Retention: Size 16: 111N (25 lbs)

Cycles: 100

### **Contact Layout**



2 pole









8 pole



12 pole

3 pole 4 pole 6 pole

### **Contact Insertion Instructions**

Step One:



Use a previously crimped contact and wire and hold just behind the contact barrel.

Step Two:



Line the contact up with the grommet.

Step Three:



Push the contact until a click is felt. Check the contact is in place by gently tugging and confirming alignment. Repeat for number of contacts desired

Step Four:



When contacts are in place, insert the appropriate wedgelock until a click is heard. Once male and female housings are prepared the parts can be mated

### XXX XX PX<sub>0</sub> X XX X

Range

PX0

**Body Type** 

100 = Male 101 = Female

102 = Male Enhanced Seal Retention 103 = Male Enhanced Seal Retention

& Protective End Cap 104 = Male Enhanced Seal Retention

& Shrink Boot Adapter 105 = Male Protective End Cap

106 = Female Protective End Cap 107 = Female Protective End Cap & Shrink Boot Adapter 108 = Male Shrink Boot Adapter

109 = Female Shrink Boot Adapter 110 = Male Terminating Resistor 111 = Terminating Resistor 112 = Female Welded Flange 113 = Female Y Type

**Contact Type** 

S = Socket P = Pin

Contacts

02 = 2 Contacts 03 = 3 Contacts

04 = 4 Contacts 06 = 6 Contacts

08 = 8 Contacts 12 = 12 Contacts Key

A = A Key

Colour

GY = Grev BK = Black