

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2069972211](#)
Status: **Active**
Overview: [CP Wire-to-Board and Wire-to-Wire Connector Systems](#)
Description: CP-4.5 Plug Housing, 4.50mm Pitch, Dual Row, 2 Circuits, Natural

Documents:
[3D Model](#) [Packaging Specification 2069960000PK-000 \(PDF\)](#)
[3D Model \(PDF\)](#) [Datasheet \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification 2069960000PS-002 \(PDF\)](#)

General
Product Family Crimp Housings
Series [206997](#)
Application Power, Wire-to-Wire
Overview [CP Wire-to-Board and Wire-to-Wire Connector Systems](#)
Product Name CP-4.5
UPC 193264462070

Physical
Circuits (maximum) 2
Color - Resin Natural (White)
Gender Plug
Glow-Wire Capable No
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 1.250/g
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 4.50mm
Pitch - Termination Interface 4.50mm
Polarized to Mating Part Yes
Temperature Range - Operating -40° to +120°C

Material Info

Reference - Drawing Numbers
Packaging Specification 2069960000PK-000
Product Specification 2069960000PS-002
Sales Drawing 2069970000-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)4578-DC (25 June 2020)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[206997 Series](#)

Mates With
CP-4.5 Receptacle Housing [2069962211](#)

Use With
Genderless Crimp Terminal 16-20 AWG [2069998000](#)
Genderless Crimp Terminal 22-26 AWG [2070008000](#)
CP-4.5 TPA [2069980100](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION