

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0469920220](#)  
**Status:** **Active**  
**Overview:** Mini-Fit Family Power Connectors  
**Description:** Mini-Fit Versa Color Receptacle Housing, Dual Row, Nylon 6/6, UL 94V-0, 2 Circuits, Glow-Wire Capable, Red

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-5557-002-000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-5556-001-001 (PDF)</a>	

**General**

Product Family	Crimp Housings
Series	<a href="#">46992</a>
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	<a href="#">Mini-Fit Family Power Connectors</a>
Product Name	Mini-Fit Versa Color
UPC	195842021457


**Physical**

Circuits (maximum)	2
Color - Resin	Red
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.680/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-5557-002-000
Product Specification	PS-5556-001-001
Sales Drawing	SD-46992-0000-000



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[46992](#) Series

**Mates With**

Mini-Fit Versa Color Plug [46993](#) . Mini-Fit Versa Color Header [172447](#)

**Use With**

Mini-Fit Female Crimp Terminal [5556](#)