

EAO – Your Expert Partner for Human Machine Interfaces

45-2844.1C90.006 - Selector switch 2 positions short lever - Actuator

45-2844.1C90.006 - Selector switch 2 positions short lever - Actuator



Attention: The preview is based on a sample product. This can differ from your current configuration.

Attribute

Design	raised
Front dimension	Ø 29,5 mm
Front form	round
IP front protection	IP66, IP67, IP69K
Mounting cut-out	Ø 22.3 mm
Front bezel colour	Black
Front bezel material	Plastic
Housing material	Plastic
Lever colour	White
Lever illumination	optional illuminative
Lever material	plastic
Lever shape	short
Rotary positions	2
Switching action	Rest - Momentary
Switching angle	45° right
Weight	0.027 kg

Schaltelement

max. number of switching elements	6
-----------------------------------	---


Function

Selector switch


EAO – Your Expert Partner for Human Machine Interfaces

45-2844.1C90.006 - Selector switch 2 positions short lever - Actuator


Dimensions



Mounting cut-outs



Wiring diagrams



Additional information

External diameter of the short lever 32.3 mm
Mounting depth, incl. front plate, see chapter drawings
External diameter of the short lever 32.3 mm