



LL-NFM-KIT-DE-C

Low ESL LL series/NFM series

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Qty
1	LLL153C80J104ME01	1005M/0402	X6S	6.3Vdc	0.1 μ F	\pm 20%	0.35max	20
2	LLL153C80J224ME14	1005M/0402	X6S	6.3Vdc	0.22 μ F	\pm 20%	0.35max	20
3	LLL153C70G474ME17	1005M/0402	X7S	4Vdc	0.47 μ F	\pm 20%	0.35max	20
4	LLL153C80G105ME21	1005M/0402	X6S	4Vdc	1 μ F	\pm 20%	0.35max	20
5	LLL1U4R60G435ME22	0610M/02404	X5R	4Vdc	4.3 μ F	\pm 20%	0.45max	20
6	NFM15PC435R0G3	1005M/0402	-	4Vdc	4.3 μ F	\pm 20%	0.5max	20
7	NFM15PC755R0G3	1005M/0402	-	4Vdc	7.5 μ F	\pm 20%	0.65max	20
8	NFM15PC915R0G3	1005M/0402	-	4Vdc	9.1 μ F	\pm 20%	0.7max	20
9	NFMJMPC156R0G3	1209M/05035	-	4Vdc	15 μ F	\pm 20%	0.65max	20
10	NFMJMPC226R0G3	1209M/05035	-	4Vdc	22 μ F	\pm 20%	0.8max	20