



Image is for illustrative purpose only

## **Cable Clamp - Compatible Cable Diameter Range - 15.9 mm | 0.625 in; Operating Temperature Range - -40 - 85 °C | -40 - 185 °F ; Black**

Item code: **22CC37D0625B**

This screw down plastic P-clip that is easy to install. Ideal for holding cables, tubes or pipes.

### **Specifications**

<b>Compatible Cable Diameter Range</b>	0.625 in
<b>Hole Diameter</b>	0.204 in

Compatible Screw Sizes (All)	10, M5
Operating Temperature Range	-40 - 185 °F
Overall Width	0.375 in
Type	1
Style	P-Clip
Material	Nylon
Adjustability	Fixed
Color	Black
Fitting Style	Clamp
Full Material	Nylon 6/6
Material Flammability Standard	UL94 V-2
Mounting Method	Screw