



## **Cable Clamp - Compatible Cable Diameter Range - 15.9 mm | 0.625 in ; Operating Temperature Range - -40 - 85 °C | -40 - 185 °F ; Natural**

Item code: **22CC37D0625**

This P-Style Natural UL94 V-0 rated nylon Loop Clamp is screw-mounted for a secure application; the cable bundle may not be removed without the screw being removed.

## **Specifications**

<b>Compatible Cable Diameter Range</b>	0.625 in
<b>Hole Diameter</b>	0.204 in
<b>Compatible Screw Sizes (All)</b>	10, M5

<b>Operating Temperature Range</b>	-40 - 185 °F
<b>Overall Width</b>	0.375 in
<b>Type</b>	1
<b>Style</b>	P-Clip
<b>Material</b>	Nylon
<b>Adjustability</b>	Fixed
<b>Color</b>	Natural
<b>Fitting Style</b>	Clamp
<b>Full Material</b>	Nylon 6/6
<b>Material Flammability Standard</b>	UL94 V-2
<b>Mounting Method</b>	Screw