



**Cable Clamp - Compatible Cable
Diameter Range - 9.5 mm | 0.375 in ;
Operating Temperature Range - -40 - 85
°C | -40 - 185 °F ; Natural**

Item code: **22CC50G0375**

This P-Style Natural UL94 V-0 rated nylon Loop Clamp is screw-mounted for a secure application; the cable bundle may not be removed without the screw being removed.

Specifications

Compatible Cable Diameter Range	0.375 in
Hole Diameter	0.250 in

Compatible Screw Sizes (All)	1/4, M6
Operating Temperature Range	-40 - 185 °F
Overall Width	0.500 in
Type	1
Style	P-Clip
Material	Nylon
Adjustability	Fixed
Color	Natural
Fitting Style	Clamp
Full Material	Nylon 6/6
Material Flammability Standard	UL94 V-2
Mounting Method	Screw