



Image is for illustrative purpose only

## **Cable Clamp - Compatible Cable Diameter Range - 3.2 mm | 0.125 in; Operating Temperature Range - -40 - 85 °C | -40 - 185 °F; Black**

Item code: **22CC50D0125B**

This screw down plastic P-clip that is easy to install. Ideal for holding cables, tubes or pipes.

### **Specifications**

|  |          |
|--|----------|
| <b>Compatible Cable Diameter Range</b> | 0.125 in |
|--|----------|

|                                       |              |
|---------------------------------------|--------------|
| <b>Hole Diameter</b>                  | 0.204 in     |
| <b>Compatible Screw Sizes (All)</b>   | 10, M5       |
| <b>Operating Temperature Range</b>    | -40 - 185 °F |
| <b>Overall Width</b>                  | 0.500 in     |
| <b>Type</b>                           | 1            |
| <b>Style</b>                          | P-Clip       |
| <b>Material</b>                       | Nylon        |
| <b>Adjustability</b>                  | Fixed        |
| <b>Color</b>                          | Black        |
| <b>Fitting Style</b>                  | Clamp        |
| <b>Full Material</b>                  | Nylon 6/6    |
| <b>Material Flammability Standard</b> | UL94 V-2     |
| <b>Mounting Method</b>                | Screw        |