



# 539EREC

Product no.: 539EREC

Narrow distance cutter with retainer for cut wires; cutting length on request



source images

Type	Type of Cut	Cutting Capacity
<b>Series 500 Medium</b>		
		mm 0,03 0,1 0,2 0,3 0,4 0,5 0,6 0,7 0,8 0,9 1,0 1,1 1,2 1,3 1,4 1,5 1,6 1,7 1,8 1,9 2,0
		Inch .0001 .0003 .0007 .0011 .0015 .0019 .0023 .0027 .0031 .0035 .0039 .0043 .0047 .0051 .0055 .0059 .0062 .0066 .0070 .0074 .0078
	512N	Semi Flush
	512E	Semi Flush
	599T	Semi Flush / Carbide
	522N	Flush
	599E	Flush
	532N	Super Full Flush
	576TX1	Flush / Carbide
	503E	Flush
	503ETST 30°	Flush / Carbide
	504AE	Flush
	555E 35°	Flush
	572E 40°	Flush
	582E 45°	Flush
	593AE 30°	Flush
	575E 45°	Flush
	592E	Flush
	792E	Super Full Flush
	576TX	Flush / Carbide
	570E	Flush
	573E	Flush
		for vertical tip cutting





**Technical Data**

Length mm	120
Length of cutting edges mm	---
Head width mm	11
Head thickness mm	6
Head length mm	26
Max. cutting capability – hard wire mm	---
Weight in oz	3.570
Length of cutting edges Inches	---
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	1.024
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	---
Max. cutting capability – copper wire mm	1.2
Length inches	4.724
Weight in g	70.2
Erem applications	---