



E147B

Product no.: E147B

Special applications – Special tool steel, ESD-safe



Side cutter with compound action.



For cutting wires with minimal effort



[source images](#)

The Perfect Cut - Strong, sharp and precise, every time

Weller Erem™ Pliers are designed to ensure an accurate and sure grip every time. Manufactured with uncompromising Swiss quality and created for worldwide applications, including electronics assembly and healthcare, Weller Erem Pliers are built to last. Feel the difference with Weller Erem™ – the proven choice. Every time.

THE PERFECT CUT

Strong, sharp and precise - every time

- + 1 Million Movements**
Magic Spring™ design enables maximum durability with constant spring force movements
- + Quality**
Uncompromising Swiss quality created to be strong, durable and sharp
- + Precision**
Experience precise cuts from the high-precision screw joint that enables a smooth action with no jaw overlap
- + Strong and Sharp**
Hand-crafted cutting edges for superior strength and sharpness
- + Comfort, Security and Grip**
Ergonomically-shaped handles provide superior comfort and fatigue-free handling with Maximum Opening Stop Technology
- ESD Safe**
Made from ESD-safe material to prevent damage to sensitive components



weller-tools.com

Weller
Erem



PRECISION
TOOLS



Technical Data

Length mm	142
Length of cutting edges mm	6
Head width mm	16
Head thickness mm	7.5
Head length mm	---
Max. cutting capability – hard wire mm	---
Weight in oz	3.527
Length of cutting edges Inches	0.236
Head width Inches	0.630
Head thickness Inches	0.295
Head length Inches	---
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	---
Max. cutting capability – copper wire mm	Ø 1,8
Length inches	5.591
Weight in g	100
Erem applications	Microelectronic