

# Han® 10 HPR HBM Rear-fit w/o frame



Part number	09 40 010 0392
Specification	Han® 10 HPR HBM Rear-fit w/o frame
HARTING eCatalogue	https://b2b.harting.com/09400100392

Image is for illustration purposes only. Please refer to product description.

#### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> HPR
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Rear mounting

Version

Locking type	Screw locking
Size	10 B
Field of application	Hoods/housings for harsh outdoor environments
Pack contents	Please order mounting frame separately.

### **Technical characteristics**

Tightening torque (screw locking)	4 Nm
Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

## Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated

Page 1 / 2 | Creation date 2021-01-21 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



#### Material properties

Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Specifications and approvals	
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
CE	Yes
Commercial data	
Packaging size	1
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors