

Han® 16 HPR HBM Rear-fit



Part number	09 40 016 0391
Specification	Han® 16 HPR HBM Rear-fit
HARTING eCatalogue	https://b2b.harting.com/09400160391

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] HPR
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Rear mounting

Version

Locking type	Screw locking
Size	16 B
Field of application	Hoods/housings for harsh outdoor environments
Pack contents	Mounting frame is included within the delivery

Technical characteristics

Tightening torque (screw locking)	4 Nm
Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated



Material properties

Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
CE	Yes

Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors